

TO UPGRADE TO BLE CONNECTED with NEW POWER SCHEME...						...PURCHASE AND INSTALL THESE MANDATORY PARTS (or REUSE as INDICATED) TO ENSURE PROPER FUNCTION											
Actuator Family	Plate Style/Color/Finish	It is a BLE connected device?*	Power	Geberit Concealed Tank Style	Tank Model	List Price Sum (2022)	Lifter	Control	Transformer kit	Power suply	Extension wire	Battery Holder					
Sigma10	Any	N	4.1V Mains AC	Sigma12(2x6)	109.304	933.00	245.551.00.6	245.539.00.6	Reuse conduit + rough-in box	243.971.00.1	244.094.00.1	-					
					109.307												
					111.335												
				111.902													
				109.797													
				109.781													
			111.798														
			111.597														
			Sigma8(2x4)	111.728	695.00	Reuse	245.540.00.6	Reuse conduit + rough-in box	243.971.00.1	244.094.00.1	-						
				111.728													
				111.728													
			3V Battery	Sigma12(2x6)	109.304							802.00	245.551.00.6	245.838.00.6	-	-	-
109.307																	
111.335																	
111.902																	
109.797																	
109.781																	
111.798																	
111.597																	
Sigma8(2x4)	111.728	695.00	NO SOLUTION - NO CONVERSION														
	111.728																
	111.728																
Sigma80	Black Glass (SG)	N	4.1V Mains AC	Sigma12(2x6)	109.304	1694.00	245.551.00.6	245.541.SG.6	Reuse conduit + rough-in box	243.971.00.1	244.094.00.1	-					
					109.307												
					111.335												
				111.902													
				109.797													
				109.781													
	111.798																
	111.597																
	Sigma8(2x4)			111.728	1456.00	Reuse							245.542.SG.6	Reuse conduit + rough-in box	243.971.00.1	244.094.00.1	-
				111.728													
				111.728													
	Mirror Glass (SM)			Sigma12(2x6)	109.304												
109.307																	
111.335																	
111.902																	
109.797																	
109.781																	
111.798																	
111.597																	
Sigma8(2x4)	111.728	1456.00	Reuse	245.542.SM.6	Reuse conduit + rough-in box		243.971.00.1	244.094.00.1	-								
	111.728																
	111.728																

**NOTES**


Blue and red color indicates connector colors of associated system - both before and after conversion  
 See below to identify if your device is not already enabled

**How to Identify Geberit CONNECT products (1/2)**

1. Packaging label



2. Electronic label



3. Bluetooth scan with Control App

